ALPHAGUARD®



Disposable Apparel

Protecting People, Products and Environments





Perfect Balance of Protection and Comfort

Features & Benefits: AlphaGuard is the result of leading-edge technologies and brings to market a unique blend of physical properties that provides both the user and your production environment with a comfortable and efficient garment. AlphaGuard is a very breathable and comfortable material for the wearer while providing a high level of filtration efficiency for your environment. A low particle count adds another measure of environmental protection for your processes. AlphaGuard material is not recommended for use with chemicals.

Coveralls White Size Blue S CV-84032-1 N/A CV-74032-2 CV-84032-2 M CV-74032-3 CV-84032-3 L CV-74032-4 XL CV-84032-4 CV-74032-5 2X CV-84032-5 CV-74032-6 3X CV-84032-6 CV-74032-7 4X CV-84032-7 CV-84032-8 CV-74032-8 5X Elastic wrist, ankle & back 25/case

Coveralls

Size

S

M

XL

2X

3X

White


CV-74832-1


CV-74832-2

CV-74832-3 CV-74832-4

CV-74832-5

CV-74832-6








CV-74832-7 CV-74832-8	4X 5X	
Elastic wrist, a AquaTrak 25/ca	c® boot	ack,

	Size	Body (A)	Chest (B)	Sleeve (C)	Leg (D)
	S	36 ½"	23"	32 ½"	28"
ns	M	37 ½"	24 1/4"	34"	28 ½"
<u>0</u>	L	38 ¾"	25"	34"	29 ½"
Dimensions	XL	40"	27"	36 ½"	30"
ne	2X	40 ½"	29 ¾"	37"	31"
	3X	43"	32"	38"	32"
	4X	43"	32 ½"	41"	32 ½"
	5X	43 ½"	33 ½"	42"	33"

Lab Coats - Knit Wrist

White	Size	Blue
LC-32632-1	S	LC-31632-1
LC-32632-2	M	LC-31632-2
LC-32632-3	L	LC-31632-3
LC-32632-4	XL	LC-31632-4
LC-32632-5	2X	LC-31632-5
LC-32632-6	3X	LC-31632-6
LC-32632-9	4X	N/A

Tapered collar, knit wrist, 3 pockets, snap close 30/case




	Size	Body (A)	Chest (B)	Sleeve (C)
S	S	36 ¾"	24 1/4"	30"
imensions	M	39 ½"	25 1⁄4"	30 1⁄4"
Si	L	40"	27"	32 ½"
e	XL	42 ¾"	27 ¾"	33"
<u>.</u> <u>E</u>	2X	43 ½"	29 ½"	37 ½"
	3X	44 ½"	30 ¾"	38 ¼"
	4X	46 ½"	31 ½"	39 1/4"



Lab Coats - Elastic Wrist

White	Size
LC-32622-1	S
LC-32622-2	M
LC-32622-3	L
LC-32622-4	XL
LC-32622-5	2X
LC-32622-6	3X
LC-32622-9	4X

Tapered collar, elastic wrist, 3 pockets, snap close 30/case




	Size	Body (A)	Chest (B)	Sleeve (C)
2	S	36 ¾"	24 1/4"	30"
imensions	M	39 ½"	25 1⁄4"	30 ¼"
<u>S</u>	L	40"	27"	32 ½"
e	XL	42 ¾"	27 ¾"	33"
<u>=</u>	2X	43 ½"	29 ½"	37 ½"
	3X	44 ½"	30 ¾"	38 ¼"
	4X	46 ½"	31 ½"	39 1⁄4"



Frocks - Elastic Wrist

White	Size	Blue
FK-32122-1	S	FK-31122-1
FK-32122-2	M	FK-31122-2
FK-32122-3	L	FK-31122-3
FK-32122-4	XL	FK-31122-4
FK-32122-5	2X	FK-31122-5
FK-32122-6	3X	FK-31122-6
FK-32122-7	4X	FK-31122-7

Raglan sleeve, elastic wrist, snap collar, snap close 30/case




	Size	Body (A)	Chest (B)	Sleeve (C)
S	S	40 ½"	21 ¾"	33 ½"
ensions	М	42 ½"	22 3/4"	34 ½"
S	L	43 ½"	23 ½"	35 ½"
	XL	46"	24 3/4"	36 ½"
<u>=</u>	2X	47 ½"	26 ½"	37 ½"
	3X	51 ½"	29"	40"
	4X	52 ½"	29 ½"	41"



Scrub Shirts - Long Sleeve

Blue	Size
WS-23221-1	S
WS-23221-2	M
WS-23221-3	L
WS-23221-4	XL
WS-23221-5	2X
WS-23221-6	3X
WS-23221-7	4X

Round neck, banded collar, elastic wrist, one pocket, safety stitched seams 30/case




	Size	Body (A)	Chest (B)	Sleeve (C)	Shoulder (D)
nS	S	17 ½"	22 ½"	20 ½"	17"
0	M	17 ¾"	24 ½"	21 ½"	18 ¼"
SU 6	L	18"	26 ½"	22 ¾"	19 1⁄4"
Dimensions	XL	18 ½"	27 ¾"	24 1⁄4"	20 ½"
٥	2X	18 ¾"	28 ½"	25 ¾"	22 1/4"
	3X	19"	30"	27"	22 ¾"
	4X	19 ½"	31 ¾"	28 ½"	24 ½"



Scrub Pants

Blue	Size
WP-23322-1	S
WP-23322-2	M
WP-23322-3	L
WP-23322-4	XL
WP-23322-5	2X
WP-23322-6	3X
WP-23322-7	4X

Spandex waist,
1 pocket, reinforced crotch,
safety stitched seams
30/case




	Size	Leg (A)	Waist Relaxed (B)	Waist Stretched (B)
Dimensions	S	38"	9 1⁄4"	16 ½"
sic	M	40 ¾"	10 1⁄4"	18 ¼"
en	L	43"	12"	21 ½"
Ë.	XL	45"	12"	21 ½"
	2X	45"	12 1⁄4"	23 ½"
	3X	46"	14 1⁄4"	25 1⁄4"
	4X	46 ½"	14 ½"	26"


Packaging Perfection

Serged Seams

This seam is produced when the threads are interlocked around the material edges for a strong stress-resistant seam.




Safety Stitched Seams An extra safety stitch is added above the serged seam to offer added strength, durability and protection.



Layered Packaging Design to Prevent Contamination from Entering Your Controlled Environment

- Packaged in a primary bag, carton liner and outer corrugated carton to prevent cross contamination and contamination migration from one environment to another
- · All garments are precision folded and stacked within the primary bag to permit efficient storage with or without bins
- · Primary bag placed in clear carton liner that is twisted and taped closed
- · All open seams on shipping containers are tape-sealed for additional protection from possible contamination
- · Four-sided carton labeling allows easy product identification and inventory management



Primary Bag, twisted & zip tied



Carton Liner



Open carton with taped down liner



Sealed carton with two corner labels

6' 10" 6' 8" 6' 6" 4X 6' 4" 3X 6' 2" 2X 6' 0" X-Large 5' 10" Large 5' 8" 5' 6" Medium 5' 4" Small 5' 2" 110 lbs. 130 lbs. 150 lbs 170 lbs. 190 lbs. 210 lbs. 230 lbs. 250 lbs 270 lbs. 290 lbs.

Please contact us for other sizing



	Standard Applied	Test Standard	AlphaGuard®	AquaTrak® Boot Covers
Material Physical Properties	Ball Burst Strength	ASTM D3787	19.1 lbs	29.8 lbs
	Bacterial Filtration Efficiency	ASTM 2101	88%	N/A
	Coefficient of Friction	ASTM D1894 Static Kinetic	N/T	0.605 0.607
	Delta P	MIL-M-36954C	3.5 mm H ₂ O/cm ²	N/A
	General Tensile	ASTM D5034 MD TD	30.75 lbs 21.3 lbs	25.94 lbs 37.58 lbs
	Helmke Drum	IEST-RP-CC003.3	Category II	Category I
	Hydrostatic Resistance	ASTM D751	N/A	31 psi
	Mass/Unit Area	ASTM D3776	47.9 g/m ²	61.2 g/m ²
	Mullen Burst Strength	ASTM D3786	143 psi	37 psi
	Puncture Propagation Tear Resistance	ASTM D2582 MD TD	4.6 lbs 7.3 lbs	6.1 lbs 8.5 lbs
	Synthetic Blood Penetration	ASTM F1670	NT	Pass
	Trapezoid Tearing Strength	ASTM D5587 MD TD	17.47 lbs 8.02 lbs	10.27 lbs 15.19 lbs
	Water Resistance Impact Penetration	AATCC Method 42	Penetration Seen	None Seen
	Water Vapor Transmission	ASTM E96	362 gm/day-m ²	7.8812 gm/day-m ²

MD - Machine Direction TD - Transverse Direction NT - Not Tested N/A - Not Applicable

Test results provided by an independent third party testing laboratory.

WARNING: These garments and associated materials are not suitable for use in some environments containing certain chemicals and/or hazardous agents. It is the responsibility of the user to determine the level of risk in a particular environment and the proper personal protection equipment needed. Garments manufactured from synthetic non-woven material may generate static electricity. Garments that contain an anti-stat treatment are not intended to be used as a safety feature. These garments are not recommended to be used in a flammable and/or explosive environment. If you have any questions, contact your distributor or Alpha Pro Tech for garment/fabric safety data. The use of this product is out of Alpha Pro Tech's control. Therefore, Alpha Pro Tech makes no warranties, expressed or implied, and assumes no liability as to the performance of these products for a particular use. **CAUTION: AVOID HEAT AND/OR OPEN FLAME.**

UCC Limited Warranty and Exclusions

Limited Warranty; Disclaimer and Limitation of Remedies: The products shall be free from defects in material and workmanship. ALPHA PRO TECH HEREBY EXPRESSLY DISCLAIMS ALL WARRANTIES, EITHER EXPRESSED OR IMPLIED, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Buyer's remedy is expressly limited to replacement of any defective product and Alpha Pro Tech shall have no responsibility for any incidental or consequential damages. Any claims under this warranty must be made in writing to Alpha Pro Tech and must be made with 90 days of the purchase.

Alpha Pro Tech, Inc. reserves the right to change any prices, terms and conditions of sale at any time without any notice.

AlphaGuard, AquaTrak and Critical Cover are registered trademarks of Alpha Pro Tech, Inc



Alpha Pro Tech is committed to protecting people, products, manufacturing and healthcare environments to optimize process effectiveness and customer profitability.

Ordering Information: To place an order, receive a sample or obtain more information, please contact our Customer Service Department toll-free from 8:30 a.m. to 5:00 p.m. Eastern Time at:

Phone: 800-749-1363 Fax: 905-479-8703 E-mail: sales@alphaprotech.com

International customers please use the following contact information:

Phone: 520-281-0127 Ext. 201 Fax: 520-281-0235 E-mail: ccrespo@alphaprotech.com

Visit us at: www.alphaprotech.com



