

45 SERIES

STANDARD VINYL



Super Heavy Duty 300 lbs, Capacity, 2.5" High Resilient Density Foam for Better Comfort, Rubber Edge Banding on Seat and Back for a good Protection of Fabric and Vinyl.

Model	Upholstery Type	Height Adjustment	Seat Dimensions	Back Dimensions	Footring	Base	Caster
A45-V	Vinyl	21"-31"	18"W x 17"D	15.5"W x 13"H	18"	Polished Aluminum	1
A47-V	Vinyl	17"-22"	18"W x 17"D	15.5"W x 13"H		Polished Aluminum	1
P45-V	Vinyl	21"-31"	18"W x 17"D	15.5"W x 13"H	18"	Black Nylon	1
P47-V	Vinyl	17"-22"	18"W x 17"D	15.5"W x 13"H		Black Nylon	1

PreFixx Group II

- 100 Vinyl Face, Poly/cotton Backing, Protective Coating for Increased Stain Resistence,
- Abrasion 400,000 Double Rubs
- Meets or Exceeds California Tech Bulletin 117, Boston Fire Dept. IX-1, Federal Standard A-A-2950, UFAC Fabric Class 1, FMVSS-302





Controls	Description	
DLC	Height and Back Tilt (This control has two levers for seat height and back angle	
	adjustment and back height adjustment with knob	
ST	Height and Seat and Back Tilt (This control has two levers, one for height adju	
	ment and the other for Seat and Back tilt adjustment and back height with	
	knob	
FLC	Three Lever for Individual Lift (Height lever adjustment, seat tilt adjustment back	
	tilt adjustment and height back adjustment with knob and a seat tension knob	







FR04 FR05 FR06

Footring	Description	
FR04	Knobless Nylon Footring 18"	
	The Footring is Loosened and Tightened by Turning the Outer Ring. (option for models 20S, 45, 50 and 60)	
FR05	Knobless Aluminum with Steel Ring 20"	
	The Footring is Loosened and Tightened by Turning the Outer Footring. (option for models 10, 20M and 20W)	
FR06	Nylon Center with Steel Ring, Footring 18" (option for models 20S, 45, 50 and 60)	



Arms	Description
TF	Fixed Height and Width, Black
TA	Fixed Height and Adjustable Width, Black
TAA	Adjustable Height and Adjustable Width



Caster	Description	
1B	Braking Caster , Recommended where Chairs may roll to easily when is Not Occupied	
1U	Soft Urethane Caster, Recommended on Tile, Cement and other Hard Surfaces	
1UB	Soft Urethane Braking Caster, Recommended for reduce Mobility when is Not Occupied	
2	Nylon Glide, Recommended for use in areas where requiring limited mobility	