



Double Plastic Bucket System

Stainless steel cart with removable handle and two 6.5 gallon (25L) polypropylene buckets

Description

With its compact design and removable handle, the 2650 cart system is as easy to maneuver as it is to store. The system can be used with two or three rectangular buckets, depending upon cleaning protocols. An extendable frame pulls out of the front of the cart to accommodate an optional third bucket that can be used for solution, or as a supplies caddy.

The durable yet lightweight cart has four heavy duty Kryptonite™ casters. The rear casters are fixed while the front caster swivel for easy steering, and can be locked to secure the cart while in use.

An included stainless steel connecting cap prevents drips between buckets. The entire system and related buckets are autoclavable at 121°C for 30 minutes.

The following optional wringers fit on this system:

- 2710 (Stainless steel downpress wringer),
- 2756 (Stainless steel flat mop wringer),
- 2767 (Stainless steel bucket wringer, flat, for Contec flat mops),
- 2768 (Stainless steel bucket wringer, curved, for EasyCurve™ mops),
- 2738 (Polypropylene bucket wringer, flat, blue),
- 2750 (Slinger™ and stainless steel frame) and
- 2766 (Stainless steel bucket wringer frame for 2768 & 2767), depending on mopping system

| Technical Information | |
|--|---|
| Materials of Construction | |
| Cart | Stainless steel, Type 304 |
| Autoclavable plastic buckets | Polypropylene / Copolymer |
| Casters | Stainless steel frames with blue Kryptonite™ autoclavable wheels |
| Finish | Electropolished |
| Dimensions | |
| Cart | L x W x H, (in / cm) 22 x 23.5 x 36 / 56 x 60 x 91 |
| Buckets | 20 x 13 x 10 / 51 x 33 x 27 |
| Additional information | |
| Available buckets | UBKT0001 (red), 25L (included) UBKT0002 (blue), 25L (included) UBKT0003 (gray), 25L (optional 3 rd bucket) |
| Replacement casters and drip cap available | |



Cart 2650

Notes:

- 1) Data shown are typical values and should not be used as product specifications.
- 2) Valid product comparison may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- 3) Current and/or comparison data may be available. Please contact a Contec sales representative for details.

Revision date: 04/28/16



Copyright © 2016 Contec, Inc. All rights reserved.

North America
P.O. Box 530
Spartanburg, SC 29304 USA
Phone: +1-864-503-8333
www.contecinc.com

Europe
ZI du Prat – RP 3707
56037 VANNES Cedex
FRANCE
+33 297 437 690

China
No.17 Longyun Road
Suzhou 215024
CHINA
+ 86-512-6274 4050