Sontara® AC Creped White Wipe

Critical task wipes

Description

Sontara AC is a white nonwoven creped wipe made with 55% special cellulose and 45% polyester. Sontara AC wipes offer extremely low lint, high strength, good absorbency and versatility. These exceptionally clean wipes contain no binders and are solvent resistant. They are durable and maintain strength, even when wet. Ideal for a wide range of critical cleaning tasks essential to industries such as biotech, pharmaceutical and electronics, they are very effective in applications such as surface preparation for coatings, machining operations, and general maintenance. Sontara AC wipes are available in 100-count single, 250-count double pop-up boxes and quarterfolded packs.

Technical Data

Attribute; (units)	Value **	Test Method		
Basis weight; (g/m²)	75.9	ASTM D3776-96		
Thickness (mils)	19	ASTM 1117		
Sheet Grab Tensile (lbs)				
Machine Direction (MD)	33	ASTM D5034-95		
Cross Direction (XD)	21	ASTM D5034-95		
Sorptive Capacity				
Intrinsic (mL/g)	4.86	ASTM D6651-01		
Extrinsic (mL/m²/s)	363	ASTM D6651-01		
Sorptive Rate				
Intrinsic (mL/g)	13.2	ASTM D6651-01		
Extrinsic (mL/m²/s)	987	ASTM D6651-01		

** ND = None detected; levels are below detection limit of test equipment

Part Number	Description	EA/OB1	OB1/CS	EA/CS
AC9165	Sontara AC Creped Wipe, 9" x 16.5" (23 x 42cm)	100	8	800
AC1212	Sontara AC Creped Wipe, 12" x 12" (30 x 30cm)	100	10	1000
AC1213	Sontara AC Creped Wipe, 12" x 13" (30 x 33cm), quarterfolded	50	10	500
AC12165	Sontara AC Creped Wipe, 12" x 16.5" (30 x 42cm), double-pop up box	125	2	250

Key: EA = Each, OB1 = Outer Bag 1, CS = Case

Notes:

- 1) The information presented here is applicable to the part numbers shown above as well as to any product containing the same materials and produced under the same conditions, regardless of product size or packaging configuration. Please contact a Contec sales representative for more details.
- 2) Data shown are typical values and should not be used as product specifications.
- y Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- 4) Boxed wipers are not tested for particles, extractables, ions and fiber shedding.
- 5) Current and/or comparison data may be available. Please contact a Contec sales representative for details.

Revision date: 07/18/08



www.contecinc.com

Europe